



# BMT DC-Controller

5 ports | 0-24VDC

- Valve or DC-pump control
- Five ports up to 24 VDC
- Control flow direction for DC-pumps
- Holding voltage option for valves
- Control latching valves
- Special PWM control for Xavitech pump on 5<sup>th</sup> port
- PWM operation for pumps on each port individually
- Program linear flow volume using PWM start and end parameters for pumps



*Start networking fluidic experiments*



### Fluidic network

Combine different BMT Controller to a fluidic network using LAN cable or Wi-Fi



### Software controlled & programmable

Easily program fluidic operations and control all devices using the BMT PC-Software.



### Stand-Alone solution

Start fluidic programs directly at the controller from an USB-Stick.



BMT Fluid Control Solutions GmbH  
Maßbornstraße 54f – D-60437 Frankfurt a. M.  
Tel.: +49 6101 95400-30 – Fax: +49 6101 95400-39

[info@pumpen-ventile.de](mailto:info@pumpen-ventile.de) – [www.pumpen-ventile.de](http://www.pumpen-ventile.de)

Specifications, etc. may be changed at any time without notice.



2018-08  
rev 1.0